




| FEATURES / APPLICATION                                                                                                                                                                                                      | PART #                                       | DESCRIPTION                                                                                                                              |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| <p><b>Porta (non-bridging) to (2) Alligator Clips, (8')</b><br/> <b>Porta (bridging) to (2) Alligator Clips, (8')</b></p> <ul style="list-style-type: none"> <li>• Test access at Porta type (coils)</li> </ul>             | <p><b>400300SP</b><br/> <b>400300SMP</b></p> | <p><b>PORTA to ALLIGATOR CLIPS</b></p>                |
| <p><b>Porta to Porta "Frogging" test cord, (10')</b></p> <ul style="list-style-type: none"> <li>• Quickly isolate trouble; cable or equipment at MDF or RT</li> <li>• "Full Duplex Frog"</li> </ul>                         | <p><b>400300F-P</b></p>                      | <p><b>PORTA "FROGGING" CORD</b></p>                   |
| <p><b>Porta to Porta "Frogger" with "In Line Protection", (20')</b></p> <ul style="list-style-type: none"> <li>• Frogger with In-Line Protection</li> <li>• Ideal for quick temporary restoral with "protection"</li> </ul> | <p><b>400300FPP</b></p>                      | <p><b>PORTA "FROGGER" w/ IN-LINE PROTECTION</b></p>  |
| <p><b>Porta to Porta "Looping" test cord, (10')</b></p> <ul style="list-style-type: none"> <li>• At "Remote Terminal" or MDF to quickly isolate troubles</li> <li>• Loops both ways</li> </ul>                              | <p><b>400300LP</b></p>                       | <p><b>PORTA "LOOPING" CORD</b></p>                  |